


Warning! The exploded views refer to the general model

General


Pos.	Code	Previous code	Description	Notes	From:	Up to:
0001	LA19430610		FIANCO SX AISI430SB ORXL			
0002	LA19430600		FIANCO DX AISI430SB ORXL			
0003	LA19430290		LID STEEL ORAC.X			
0004	LA19120130		UPPER BACK ORAC.B			
0005	LAR19120120		BACK INF. ORAC.B XL			
0006	LA19201060		FILTER [C] AIR ORAC.B			
0006	LA19220890		AIR FILTER ETL ORAC.B	ETL		
0007	LA85010410		SEAL H10 L5000	3,6 m		
0008	LAR19101510		KIT WAVE GUIDE COVERS ORACB V. 3			
0009	LAR19101340		KIT W.G. COVER BRACKETS ORAC V.3			
0010	LAR19101500		KIT PLATE FOOTS ORAC 4.0			



Warning! The exploded views refer to the general model

Door

Pos.	Code	Previous code	Description	Notes	From:	Up to:
00P1	LA19120050		PREM.PORTA LX INOX 3.0 ORXL			
00P2	LA69017720		HANDLE [C] DOOR ORAC.B LAINOX			
00P3	LA19201650		EXT.DOOR(L HINGES) LAINOX			
00P4	LAR19201010		HINGE ORAC.B (2x)			
00P5	LAR19100690		INTERLOCK [C] LEFT ORAC.B			
00P6	LAR19100700		INTERLOCK [C] RIGHT ORAC.B			
00P7	LAR19120040		INNER DOOR ORAC X			
00P8	LA65260840		MICRO [C] DOOR SWITCH			



Warning! The exploded views refer to the general model

Control panel

Pos.	Code	Previous code	Description	Notes	From:	Up to:
00C1	LA19220200		ASS.CRUSCOTT.ORXL VERNICIATO NERO			
00C2	LA70040040		GASKET [C] DYSPLAY 7			
00C3	LAR19101360		LOUDSPEAKER 4 OHM ORAC.B			
00C4	LAR65303600		BOARD DISPLAY ORAC.B			
00C5	LAR65303550		MAIN BOARD ORAC.X			
00C6	LA65280290		NTC B57881S 3460K 10 KOHM			
00C7	LA65302600		CABLE [C] BOARD/USB OUTLET L. 850			
00C8	LA65303640		CABLE [C] ETHERNET L MIN=1mt 90°			
00C9	LAR65303070		PLUG [C] ETHERNET F/F			
00E1	LAR19100530		KIT HV CAPACITOR 50HZ ORAC.B	50 Hz		
00E1	LAR19100660		ELECTRIC CONDENSER 60HZ ORAC.B	60 Hz		
00E1	LAR19100980		KIT COND+FUSIBILE HV 60HZ ETL ORM	ETL		
00E2	LA19200820		TRANSFORMER [C] HV AC 230V 50HZ ORAC.B	50 Hz		
00E2	LA65187321		TRANSFORMER HV ORAC.B 208-240V 60Hz	60 Hz		
00E3	LA65187310		POWER SUPPLY 15V 3A ORAC.B			
00E4	LAR65070540		THERMOSTAT [C] ORAC.B			
00E5	LA65210020		FUSE HOLDER [C] 5X20			
00E6	LAR19100730		TERMINAL BLOCK [C] ORAC.B			
00E7	LA19100480		ASS.ELECTRIC [C] ORAC.B			
00E8	LA65140900		CONTACTOR [C] 3RT2016-1AP02			
00E9	LA65210130		FUSE HOLDER [C] HV			
00S1	LA65303562		BOAD EXP. MAGNETRON ORAC.X			
00S2	LAR19101310		MAGNETRON R. ORAC.B			
00S3	LA65303580		BOARD [C] FILTER EMI ORAC.B			
00S4	LA65301750		CABLE [C] SERIAL RJ45 L. 600			
00S5	LAR19101320		BOARD ARCDETECTOR ORAC2			
00S6	LAR19101300		MAGNETRON L. ORAC.B			
0E11	LAR19100670		KIT FUSES ORAC.B			
0E12	LA19201890		PREM.VENT.RAFFR.WG 71W ETL ORM/ORXL	ETL		
0E12	LA19221600		PREM.VENT.RAFFR.WG 71W ORM/ORXL			
0E13	LA19400610		FILTER [C] CATALYST ORAC.B			
0E14	LAR65012440		HEATING ELEMENT [C] 2800W 230V ORAC.B	230 V		
0E14	LAR65012450		HEATING ELEMENT 2800W 208V ORAC.B	208 V		
0E15	LAR19200830		MOTOR [C] FAN ORAC.B			
0E15	LAR19221140		MOTOR [C] FAN ORAC.B ETL	ETL		
0E16	LAR19201250		PROBE [C] K 0,8M			

Pos.	Code	Previous code	Description	Notes	From:	Up to:
0E17	LAR19100770		KIT GASKETS ORAC.B			
0E19	LA65303940		POWER SUPPLY BOARD ORAC			